

Luminance Contrast Report

Product: Carpex Broadloom Carborundum Stair Nosing

Product Code: SN-CAGBL - Various

Address: 8a Lara Way, Campbellfield VIC 3061

Testing Date: 29/09/2022

We have determined the luminance contrast of the following sample. These test results and report should be used as a good guidance only with the test method specified in the standards AS/NZS 1428.1.2009 Appendix B3.

Product

Product Name: Carpex Broadloom

Carborundum Stair Nosing

Product Description:

Aluminium Stair Nosing to suit Broadloom Carpet Tile with Carborundum Tape Insert



Test Results

Overall view of test results per colour - Please see table of results on next page

Colour	Dry LRV Average	Wet LRV Average
Black	2.959	1.972
Grey	15.474	15.475
White	74.180	73.081
Yellow	40.700	40.070





	•			
126			OCIL	+-
		I R V R		_
1 4 5		LRV R		

Dry Measurements		Wet Measurements		Dry Measurements			Wet Measurements			
Colour	Black					Colour	Grey			
2.918	2.924		2.295	2.031		15.432	15.019		16.213	15.538
2.926	2.926		2.179	1.893		15.622	15.48		15.322	15.59
2.9	3.032		2.185	1.846		15.35	15.433		15.455	15.597
3.067	2.965		2.115	1.875		15.912	15.114		15.204	15.325
2.926	2.979		1.897	1.778		15.554	15.668		15.647	15.092
3.041	2.91		1.918	1.863		15.469	15.846		15.401	15.353
3.015	2.948		1.891	1.906		15.334	15.411		15.323	15.501
2.914	2.953		2.007	1.952		15.499	15.639		15.391	15.635
3.039	2.92		2.029	1.904		15.668	15.356		15.224	15.804
3.037	2.845		2.017	1.856		15.39	15.279		15.466	15.423
Mean Dry		9	Mean Dry	4- 4-4	-	Mean				
LRV	2.959		Wet LRV	1.972		LRV	15.474		Wet LRV	15.475
Colour	White					Colour	Yellow			
74.487	74.409		73.382	73.197		40.784	40.3		40.583	40.372
74.423	74.059		72.207	73.536		40.324	40.401		40.446	39.816
74.527	73.399		73.886	73.383		41.257	40.862		40.324	40.123
74.403	73.689		73.677	74.001		40.985	41.31		39.901	39.793
74.146	74.388		73.266	73.704		40.517	40.406		40.098	39.412
74.03	74.431		73.389	74.083		40.569	40.472		39.921	38.926
73.326	74.508		72.84	73.083		40.855	40.93		40.065	40.365
74.216	73.971		72.038	71.437		41.38	40.794		40.396	40.393
74.508	73.561		73.031	72.071		40.255	40.724		39.993	40.26
74.612	74.513		73.326	72.087		40.706	40.161		40.221	39.995
Mean Dry LRV	74.180		Mean Wet LRV	73.081	•	Mean Dry LRV	40.700		Mean Wet LRV	40.070



Term	Definition			
Luminance contrast	The light reflected from one surface or component, compared to the light			
	reflected from another surface or component.			
LRV	Luminance reflective value			
Bowman-Sapolinski	To determine the luminance contrast between the samples tested, the			
equation	LRVs are entered into the Bowman-Sapolinski equation:			
	C = 125 (Y2 - Y1)/(Y1 + Y2 + 25), where:			
	C = luminance contrast			
	Y1 and Y2 = LRV of each surface			
TGSI	Tactile Ground Surface Indicator			
Integrated TGSI	Tactile ground surface indicators that are in a defined pattern and which			
	are of the same luminance and material as the base surface.			
Discrete TGSI	Individually installed TGSIs, which provide the same luminance for the			
	sloping sides and upper surface of the truncated cone.			
Composite Discrete	Tactile ground surface indicators that are individually installed and which			
TGSI	provide a differing luminance for the sloping sides and upper surface of the			
	truncated cone.			
Stair Nosing	A strip not less than 50 mm and not more than 75 mm deep across the full			
	width of the path of travel.			

Laboratory Testing Equipment

Sterling Supplies uses compliant testing apparatus meeting AS/NZS 1428.1.2009 Appendix B3.2 requirements:

- Model: Konica Minolta CR-400 Tristimulus Colorimeter
- Illuminating and viewing system: Diffuse illumination/0<° (d/0) viewing angle, specular component included.
- Light source: Pulsed xenon lamp
- Minimum measurement interval: 3 seconds
- Measurement / illumination area 8mm Diameter
- Illuminant used: CIE Standard Illuminant D65

Testing Methodology

The following is a summary of the testing methodology, conducted in accordance with requirements of AS/NZS 1428.1.2009, Appendix B3.3:

- The apparatus was calibrated in accordance with the manufacturer's
- The tristimulus value 'Y' (LRV measurements) were taken of the surface in random locations in dry & wet conditions.
- 20 measurements were taken. See table of results.
- Surface area was swept with a rag to remove dust particles and soiling
- Wet Measurements were determined after 5 minutes of water ponding on the surface.

